

Compact cylinder ADN-40-5-A-P-A

Part number: 536289

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Stroke | 5 mm |
| Piston diameter | 40 mm |
| Piston rod thread | M10x1.25 |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 21287 |
| Piston rod end | External thread |
| Position sensing | For proximity sensor |
| Symbol | 00991217 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1 MPa |
| Operating pressure | 0.6 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1 |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.7 J |
| Theoretical force at 6 bar, retracting | 686 N |
| Theoretical force at 6 bar, advancing | 754 N |
| Moving mass | 107 g |
| Product weight | 380 g |
| Type of mounting | With through-hole With internal thread With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Flange screws material | Steel |
| Cover material | Wrought aluminum alloy, anodized |
| Seals material | TPE-U(PUR) |
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | Wrought aluminum alloy, smooth-anodized |