

# Compact cylinder ADN-16-50-A-P-A

Part number: 536331

FESTO



 General operating condition

## Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	16 mm
Piston rod thread	M6
Based on norm	ISO 21287
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Position sensing	Via proximity switch
Symbol	00991217
Variants	Piston rod at one end
Operating pressure	0.06 MPa ... 1 MPa
Operating pressure	0.6 bar ... 10 bar
Operating pressure	8.7 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.15 J
Theoretical force at 6 bar, retracting	90 N
Theoretical force at 6 bar, advancing	121 N
Moving mass	38 g
Product weight	145 g
Type of mounting	With through-hole With internal thread With accessories
Pneumatic connection	M5
Note on materials	RoHS compliant
Flange screws material	Steel
Cover material	Wrought aluminum alloy, anodized
Seals material	TPE-U(PUR)
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized