

# Vacuum generator VN-10-L-T4-PQ2-VQ2-O2-P

Part number: 536807

FESTO



General operating condition

## Data sheet

Feature	Value
Nominal width of Laval nozzle	0.95 mm
Width dimension	16 mm
Muffler construction type	Open
Mounting position	Any
Ejector characteristics	High suction flow Standard
Integrated function	Pressure sensor Muffler open
Structural design	T-shape
Short-circuit protection	Pulsed
Measured variable	Relative pressure
Measuring principle	Piezoresistive
Method of measurement	Relative
Switching element function	N.O. contact
Switching function	Threshold value comparator Threshold value with variable hysteresis
Symbol	00991917
Reverse polarity protection	for all electrical connections
Display type	LED
Setting range threshold value	-0.1 MPa ... 0 MPa
Setting options	Teach-in
Switching status indication	LED
Setting range threshold value	-1 bar ... 0 bar
Threshold value setting range	-14.5 psi ... 0 psi
Operating pressure for max. suction rate	0.5 MPa
Operating pressure for max. suction rate	5 bar
Operating pressure for max. suction rate	72.5 psi
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Nominal operating pressure	0.6 MPa
Nominal operating pressure	6 bar
Nominal operating pressure	87 psi
Max. suction rate with respect to atmosphere	41.5 l/min
Switch-off time	≤4 ms
On time	≤4 ms

Feature	Value
DC operating voltage range	15 V ... 30 V
Inductive protective circuit	Adapted to MZ, MY and ME coils
Max. output current	100 mA
Residual current	≤0.3 mA
Residual ripple	10%
Switching output	PNP
Voltage drop	≤1.5 V
Overload protection	Available
Certification	RCM compliance mark
KC characters	KC-EMV
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C ... 60 °C
Cleaning advice	Soap suds
Noise level at nominal operating pressure	66 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Max. tightening torque	0.6 Nm
Pressure measuring range	-0.1 MPa ... 0 MPa
Pressure measuring range	-1 bar ... 0 bar
Pressure measuring range	-14.5 psi ... 0 psi
Product weight	36 g
Accuracy in ± % FS	1.5 %FS
Long-term drift	±0.5% FS max.
Temperature coefficient of switching point	0.05 %/K
Electrical connection	M8
Type of mounting	With through-hole
Pneumatic connection 1	QS-6
Pneumatic connection 3	Muffler open
Vacuum connection	QS-6
Seals material	NBR
Female nozzle material	POM
Housing material	Reinforced POM
Fiber-optic cable	PC
Muffler material	Protective grounding
Material of plug housing	Chrome-plated and nickel-plated
Material of jet nozzle	Wrought aluminum alloy
Material of keypad	POM
Material of pneumatic fitting	Brass Nickel-plated