


Proximity sensor SIEH-3B-NS-S-L

Part number: 538265

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Symbol	00991703
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	according to UK RoHS regulations (UK-R)
Measuring principle	Inductive
Rated operating distance	1 mm
Assured operating distance	0.81 mm
Reduction factors	Aluminum = 0.5 Stainless steel St 18/8 = 0.8 Copper = 0.45 Brass = 0.6 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy	0.02 mm
Switching output	NPN
Switching element function	N/O contact
Hysteresis	≤0.12 mm
On time	0.02 ms
Max. switching frequency DC	3000 Hz
Max. output current	100 mA
Voltage drop	≤2 V
Inductive protective circuit	Installed Output current <100 mA and switching frequency < 10 Hz
Residual current	≤0.1 mA
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Residual ripple	20 %
Idle current	≤10 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	not rotatable

Feature	Value
Electrical connection 1, type of mounting	Compatible with snap-locking Compatible with rotatable screw-type lock
Cable length	0.15 m
Material of cable sheath	TPE-U(PUR)
Insulating sheath material	PVC
Size	3 mm
Type of mounting	Clamped
Mounting type	Flush
Product weight	4 g
Housing material	High-alloy stainless steel
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP67
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Selection of additional sensor information	With increased switching distance
Electrical output	NPN
Selection of sensor version	Standard