

Air line lubricator MS12-LOE-G-U

Part number: 537156

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical $\pm 5^\circ$
Structural design	Proportional standard oil mist lubricator
Max. oil capacity	1500 cm ³
Bowl guard	Integrated as metal bowl
Symbol	00991532
Operating pressure	1 bar ... 16 bar
Minimum flow rate for lubricator function	400 l/min
Normal nominal flow rate (normalized to DIN 1343)	20000 l/min ... 22000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Temperature of medium	0 °C ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 °C ... 60 °C
Product weight	6500 g
Type of mounting	With retaining bracket
Pneumatic connection 1	Internal
Pneumatic connection 2	Internal
Covering material	PA
Seals material	NBR
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy