

Proximity sensor SIEH-M18B-PS-K-L-CR

Part number: 538256

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991702
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	according to UK RoHS regulations (UK-R)
Rated operating distance	10 mm
Assured operating distance	8.1 mm
Reduction factors	Aluminum = 1.0 Stainless steel, 1 mm thick = 0.4 Stainless steel, 2 mm thick = 0.8 Copper = 0.8 Brass = 1.3 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Switching output	PNP
Switching element function	N.O. contact
Reproducibility, switching value FS	0.5 mm
Hysteresis	≤1.22 mm
Max. switching frequency	200 Hz
Max. output current	200 mA
Voltage drop	2 V
Inductive protective circuit	Installed Output current <100 mA and switching frequency < 10 Hz
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Residual ripple	20%
Idle current	<12 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Material of cable sheath	TPE-U(PUR)
Size	M18
Type of mounting	With locknut
Mounting type	Flush

Feature	Value
Product weight	115 g
Housing material	High-alloy steel
Switching status indication	Yellow LED
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP67 IP69K
Resistance to sensor fitting pressure	60 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Selection of additional sensor information	With increased switching distance
Electrical output	PNP
Selection of sensor version	Fully stainless steel housing