

Electric cylinder EPCC-BS-32-50-8P-A

Part number: 5428842

FESTO



 General operating condition

Data sheet

Feature	Value
Size	32
Stroke	50 mm
Stroke reserve	0 mm
Piston rod thread	M8
Reversing backlash	100 µm
Screw diameter	8 mm
Spindle pitch	8 mm/U
Max. angle of rotation of the piston rod +/-	1 deg
Mounting position	Any
Piston rod end	External thread
Motor type	Stepper motor Servo motor
Position sensing	Via proximity switch
Structural design	With ball screw
Spindle type	Ball screw
Symbol	00991941
Protection against torsion/guide	With plain bearing-guide
Max. acceleration	15 m/s ²
Max. rotational speed	3750 rpm
Max. speed	0.5 m/s
Max. homing speed	0.01 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 9 according to ISO 14644-1
Storage temperature	-20 °C ... 60 °C
Relative air humidity	Non-condensating
Degree of protection	IP40
Ambient temperature	0 °C ... 60 °C
Impact energy in the end positions	0.0036 J
Max. driving torque	0.3 Nm
Max. torque Mx	0 Nm
Max. torque My	1.5 Nm
Max. torque Mz	1.5 Nm

Feature	Value
Max. radial force on actuator shaft	75 N
Max. feed force Fx	150 N
No-load driving torque	0.095 Nm
Guide value for payload, horizontal	24 kg
Guide value for payload, vertical	12 kg
Mass moment of inertia JH per meter of stroke	0.0311 kgcm ²
Mass moment of inertia JL per kg of payload	0.0162 kgcm ²
Mass moment of inertia JO	0.0055 kgcm ²
Maintenance interval	Lifetime lubrication
Moving mass at 0 mm stroke	98 g
Additional moving mass per 10 mm stroke	3.3 g
Basic weight with 0 mm stroke	225 g
Additional weight per 10 mm stroke	24 g
Type of mounting	With internal thread With accessories
Note on materials	RoHS compliant
Housing material	Smooth-anodized
Piston rod material	high-alloy stainless steel
Ball screw nut material	Steel
Spindle material	Bearing steel