

# Handling module HSW-16-AS

Part number: 540238

FESTO



 General operating condition

## Data sheet

Feature	Value
Working stroke	20 mm ... 35 mm
Size	16
Max. linear stroke at 90° swivel angle	175/175 mm
Z-stroke	80 mm ... 100 mm
Cushioning	Acoustic insulation via buffers
Mounting position	Any
Structural design	Linear guide plus ball bearing Positively driven motion sequence
Position sensing	For proximity sensor
Repetition accuracy end positions	+/-0.02 mm
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. driving torque on actuator shaft	2.5 Nm
Max. axial force at actuator shaft	30 N
Max. torque Mx	2.5 Nm
Max. torque My	2.5 Nm
Max. torque Mz	2.5 Nm
Max. payload	1.5 kg
Max. radial force on actuator shaft	75 N
Maximum process force in y direction	50 N
Product weight	4900 g
Type of mounting	Via through-hole and centering sleeve
Stops material	High-alloy steel
Spring pressure piece material	High-alloy steel
Base plate material	Wrought aluminum alloy Anodized
Retainer bracket material	Anodized
Cross guide material	Tempered steel
Swivel lever material	Case-hardened steel Burnished
Link material	Case-hardened steel Hardened
Sensor rail material	Wrought aluminum alloy Anodized
Fixed link material	Wrought aluminum alloy Anodized
Setting screw material	High-alloy steel