


Pressure sensor VMPA-FB-PS-P1

Part number: 541087

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Symbol	00992805
Certification	c UL us - recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS compliant
Measured variable	Relative pressure
Method of measurement	Piezoresistive pressure sensor with display
Pressure measuring range	0 MPa ... 1 MPa
Pressure measuring range	0 bar ... 10 bar
Pressure measuring range	0 psi ... 145 psi
Pressure measuring range initial value	0 MPa
Pressure measuring range initial value	0 bar
Pressure measuring range initial value	0 psi
Pressure measuring range end value	1 MPa
Pressure measuring range end value	10 bar
Pressure measuring range end value	145 psi
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Pressure resolution	0.001 bar
Accuracy in ± % FS	2.5 %FS
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 25%
Reverse polarity protection	For operating voltage
Electrical connection	Via sub-base
Mounting position	Any
Pneumatic connection	M7
Product weight	200 g
Housing material	Die-cast aluminum PA-GF
Display type	LED
Displayable unit(s)	KPa mbar psi
Switching status indication	LED

Feature	Value
Setting range threshold value	0 % ... 100 %
Setting range threshold value	0 bar ... 10 bar
Setting range hysteresis	0 % ... 100 %
Setting range hysteresis	0 bar ... 10 bar
Degree of protection	IP65
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L