

# Air solenoid valve CDVI5.0-MT2H-1X3OLS-EXT

Part number: 547014

FESTO



General operating condition

## Data sheet

Feature	Value
Valve function	3/2-way, monostable, open
Actuation type	Electrical
Normal nominal flow rate (normalized to DIN 1343)	500 l/min
Pneumatic working port	Sub-base
Operating voltage	24V DC
Operating pressure	-0.9 bar ... 10 bar
Structural design	Piston gate valve
Reset method	Pneumatic spring
Nominal width	5 mm
Exhaust air function	Adjustable
Sealing principle	Soft
Manual override	Non-detenting
Type of control	Piloted
Pilot air supply port	External
Flow direction	Reversible
Symbol	00991789
Note on forced dynamization	Switching frequency at least once a month
Pilot pressure	3 bar ... 8 bar
b-value	0.34
C value	2.05 l/sbar
Switching time off	14 ms
On switching time	10 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Product weight	185 g
Type of mounting	Screw-in
Pilot exhaust air port 82/84	Sub-base
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Pneumatic connection 3	Sub-base
Pneumatic connection 4	Sub-base
Pneumatic connection 5	Sub-base

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS compliant
Seals material	NBR TPE-O
Housing material	Die-cast aluminum