


Diffuse scan SOEG-RT-M12-PS-S-2L

Part number: 547909

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Symbol	00991641
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Reflection light sensor
Type of light	Red
Working range	70 mm ... 300 mm
Ambient temperature	-25 °C ... 55 °C
Switching output	PNP
Switching element function	Bright-switching
Hysteresis	≤30 mm
Max. switching frequency	1000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 36 V
Residual ripple	20 %
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Electrical connection	M12x1 Plug
Size	M12
Type of mounting	With lock nut
Tightening torque	10 Nm
Mounting position	Any
Product weight	20 g
Housing material	Chrome-plated
Switching status indication	LED yellow
Function reserve indication	LED green
Setting options	Potentiometer

Feature	Value
Setting range, lower limit	70 mm
Setting range, upper limit	300 mm
Ambient temperature with flexible cable installation	-5 °C ... 55 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III