

Proximity sensor SIES-8M-PO-24V-K-7,5-OE

Part number: 551391

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Design	For T-slot
Conforms to standard	EN 60947-5-2
Symbol	00991613
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC characters	KC-EMV
Note on materials	RoHS compliant
Measured variable	Position
Measuring principle	Inductive
Rated operating distance	1.5 mm
Reduction factors	Aluminum = 0.62 Stainless steel V2A = 0.95 Copper = 0.6 Brass = 0.72 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy under constant conditions	≤ 0.05 mm, approach from the side
Switching output	PNP
Switching element function	NC contact
On time	≤ 1.0E-4 ms
Max. switching frequency	4500 Hz
Max. output current	150 mA
Max. switching capacity DC	4.5 W
Voltage drop	≤ 2 V
Inductive protective circuit	Installed
Minimum load current	0 mA
Residual current	≤ 0.01 mA
Short-circuit protection	Pulsed
Overload protection	Available
DC operating voltage range	10 V ... 30 V
Residual ripple	10%
Idle current	≤ 10 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable

Feature	Value
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connection outlet orientation	Longitudinal
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Energy chain: > 5 million cycles, bending radius 75 mm
Cable length	7.5 m
Cable characteristic	Standard/suitable for energy chains
Color cable sheath	Gray
Material of cable sheath	TPE-U(PU)
Insulating sheath material	PVC
Size	Slot 8
Type of mounting	Flush with T-slot Screwed on Can be inserted in slot from above
Tightening torque	0.6 Nm
Mounting position	Any
Mounting type	Flush
Housing colour	Black
Housing material	PUR high-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP65 IP67
Insulation voltage	50 V
Surge resistance	0.8 kV
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1
Contamination level	3
Selection of additional sensor information	For T-slot
Electrical output	PNP
Selection of sensor version	Special design