



Air preparation combination unit MSB4N-1/4:C3J1M1D7A1F3-WP

Part number: 550484

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 4 |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manually rotating |
| Structural design | Branching module Soft-start valve Pressure switch On/off valve Filter regulator with pressure gauge |
| Controller function | Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function |
| Bowl guard | Plastic bowl guard |
| Symbol | 00991760 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 4,5 bar ... 10 bar |
| Pressure regulation range | 4 bar ... 9 bar |
| Normal nominal flow rate (normalized to DIN 1343) | 600 l/min |
| Coil characteristics | 24 V DC: 1.8 W |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -10 °C ... 60 °C |
| For use in the food industry | See supplementary material information |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:-] |
| Temperature of medium | -10 °C ... 50 °C |
| Ambient temperature | -10 °C ... 50 °C |
| Product weight | 2200 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | 1/4 NPT |
| Pneumatic connection 2 | 1/4 NPT |

| Feature | Value |
|------------------------|-------------------|
| Pneumatic connection 3 | G1/4 1/4 NPT |
| Housing material | Die-cast aluminum |
| Material of bowl | PC |