

# Electrical interface CPV14-GE-ASI-4E4A-Z-M8-CE

Part number: 552561

FESTO



 General operating condition

## Data sheet

Feature	Value
Fieldbus interface	AS-Interface: flat cable plug Load voltage: flat cable plug
Device-specific diagnostics	Short circuit/overload of inputs
Max. no. of valve positions	4
Max. no. of solenoid coils	4
Reverse polarity protection	for all electrical operating voltage connections
Number of slaves per device	1
AS-Interface DC operating voltage range	26.5 V ... 31.6 V
Debounce time at inputs	3 ms
Information concerning load voltage	Via load voltage connection (24 V DC)
Load voltage range DC	21.6 V ... 26.4 V
Max. number of inputs	4
Nominal operating voltage DC AS-Interface	26.5 V
Nominal voltage DC	24 V
AS interface residual ripple	20 mV <sub>SS</sub>
Load voltage residual ripple	4 V <sub>SS</sub>
Switching level	Signal 0: ≤ 5 V Signal 1: ≥ 11 V
Current consumption with load voltage from AS-Interface and load voltage connection	Inputs: 200 mA Electronics: 20 mA Valves: 175 mA (depending on pneumatic valve type)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 70 °C
Relative air humidity	Non-condensating
Degree of protection	IP65 In mounted state
Ambient temperature	-5 °C ... 50 °C
Product weight	233 g
Input characteristics	As per IEC 1131-2, type 02
Input switching logic	PNP (positive switching)
Addressing range	1A ... 31A (0) 1B ... 31B Setting using AS-Interface addressing device
Galvanic isolation fieldbus interface	Optocoupler
LED display (bus-specific)	AS-i: AS-Interface operation Aux/Pwr: AS-Interface power supply Error: AS-Interface error

<b>Feature</b>	<b>Value</b>
LED display (product-specific)	0 ... 3: switching status of inputs 12/14: switching status of pneumatic valves (on pneumatic valve)
Product identification	ID code: ID=Ah, ID1=7h, ID2=7h IO code: 7h Profile: S-7.A.7
Cover material	PA-reinforced
Seals material	CR NBR
Housing material	Die-cast aluminum
Note on materials	RoHS compliant