



Pressure booster DPA-63-10-CRVZS10

Part number: 552932

FESTO



 General operating condition

Data sheet

Feature	Value
Piston diameter	63 mm
Volume	10 l
Mounting position	Condensate drain downwards
Structural design	with air reservoir with pressure gauge with non-return valve
Symbol	00991432
Pressure gauge	with pressure gauge
Output pressure 2	0.4 MPa ... 1 MPa
Outlet pressure 2	4 bar ... 10 bar
Output pressure 2	58 psi ... 145 psi
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Operating pressure	29 psi ... 116 psi
Pressure regulation range MPa	0.4 MPa ... 1 MPa
Pressure regulation range	4 bar ... 10 bar
Pressure regulation range psi	58 psi ... 145 psi
Inlet pressure 1	2 bar ... 8 bar
Inlet pressure 1 MPa	0.2 MPa ... 0.8 MPa
Inlet pressure 1 psi	29 psi ... 116 psi
CE marking (see declaration of conformity)	as per EU pressure equipment directive
UKCA marking (see declaration of conformity)	according to UK regulations for pressure equipment
Operating medium	Compressed air as per ISO 8573-1:2010 [7:3:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Max. tightening torque for condensate drain	27 Nm
Product weight	16000 g
Type of mounting	With slot nuts
Pneumatic connection 1	QS-12
Pneumatic connection 2	KD4

Feature	Value
Pneumatic connection 3	Pneumatic muffler
Note on materials	RoHS-compliant
Air reservoir material	High-alloy stainless steel