

Micro filter MS9-LFM-N1-AUV-HF

Part number: 553056

FESTO



 General operating condition

Data sheet

Feature	Value
Series	MS
Size	9
Structural design	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	Manual, non-detenting
Symbol	00991520
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:-:4]
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [3:-:2]
Max. standard flow rate for air quality class	7800 l/min
Min. standard flow rate for air quality class	390 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99.995 %
MPPS	0.1 µm
MPPS filter efficiency	99.968 %
Residual oil content	0.01 mg/m ³
Filter efficiency, oil aerosol	99 %
Type of mounting	With accessories
Mounting position	Vertical +/- 5°
Pneumatic connection 1	1 NPT
Pneumatic connection 2	1 NPT
Housing material	Die-cast aluminum
Covering material	PA
Compressed air filter material	Borosilicate fiber
Material of bowl	Wrought aluminum alloy
Inspection window material	PA

Feature	Value
Seals material	NBR
Product weight	2500 g