


# Compact cylinder ADNGF-63-30-P-A

Part number: 554272

FESTO



 General operating condition

## Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	63 mm
Based on norm	ISO 21287
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Protection against torsion/guide	Guide rod with yoke
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	1.3 J
Theoretical force at 6 bar, retracting	1750 N
Theoretical force at 6 bar, advancing	1870 N
Moving mass	485 g
Product weight	1145 g
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Flange screws material	Steel
Cover material	Wrought aluminum alloy, anodized
Seals material	TPE-U(PUR)
End plate material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized