

Swivel actuator unit DSL-16-40-270-P-A-S20-B

Part number: 556399

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg ... 270 deg
Stroke	40 mm
Piston diameter	16 mm
Swivel angle	0 deg ... 272 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Precision adjustment	-6 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	Via proximity switch
Symbol	00991269
Variants	Through, hollow piston rod
Protection against torsion/guide	With plain bearing-guide
Operating pressure	2.5 bar ... 8 bar
Max. impact velocity	0.5 m/s
Max. swivel frequency at 6 bar	2 Hz
Swivel angle backlash	2 deg
Repetition accuracy	1 deg
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Dynamic load torque	0.1 Nm
Theoretical force at 6 bar, retracting	73.5 N
Theoretical force at 6 bar, advancing	102.5 N
Theoretical torque at 6 bar	1.25 Nm
Permissible mass moment of inertia	3.5E-5 kgm ²
Product weight	827 g
Basic weight with 0 mm stroke	695 g
Additional weight per 10 mm stroke	33 g
Type of mounting	Clamped in T slot With external thread
Pneumatic connection	M5
Cover material	Wrought aluminum alloy Anodized

Feature	Value
Seals material	TPE-U(PU)
Housing material	Smooth-anodized
Piston rod material	Quenched and tempered steel