

# Swivel actuator unit DSL-16-50-270-P-A-S2-KF-B

Part number: 556594

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Adjustment range of swivel angle         | 0 deg ... 270 deg  |
| Stroke                                   | 50 mm  |
| Piston diameter                          | 16 mm  |
| Swivel angle                             | 0 deg ... 272 deg  |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Precision adjustment                     | -6 deg   |
| Mode of operation                        | Double-acting  |
| Structural design                        | Rotary vane  |
| Position sensing                         | For proximity sensor   |
| Symbol                                   | 00991268   |
| Variants                                 | Through piston rod   |
| Protection against torsion/guide         | Guided on ball bearings  |
| Operating pressure                       | 2.5 bar ... 8 bar  |
| Max. impact velocity                     | 0.5 m/s  |
| Max. swivel frequency at 6 bar           | 2 Hz   |
| Swivel angle backlash                    | 0.05 deg   |
| Repetition accuracy                      | 1 deg  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Ambient temperature                      | -10 °C ... 60 °C   |
| Dynamic load torque                      | 0.17 Nm  |
| Theoretical force at 6 bar, retracting   | 73.5 N   |
| Theoretical force at 6 bar, advancing    | 103.5 N  |
| Theoretical torque at 6 bar              | 1.25 Nm  |
| Permissible mass moment of inertia       | 3.5E-5 kgm <sup>2</sup>  |
| Product weight                           | 910 g  |
| Basic weight with 0 mm stroke            | 745 g  |
| Additional weight per 10 mm stroke       | 33 g   |
| Type of mounting                         | Clamped in T slot<br>With external thread                          |
| Pneumatic connection                     | M5   |
| Cover material                           | Wrought aluminum alloy<br>Anodized                                 |

| <b>Feature</b>      | <b>Value</b>    |
|---------------------|-----------------|
| Seals material      | TPE-U(PU)       |
| Housing material    | Smooth anodized |
| Piston rod material | Tempered steel  |