

Round cylinder DSNU-32-80-PPS-A

Part number: 559298

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Stroke | 80 mm |
| Piston diameter | 32 mm |
| Piston rod thread | M10x1.25 |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | Any |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | For proximity sensor |
| Symbol | 00992970 |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.4 J |
| Cushioning length | 14 mm |
| Theoretical force at 6 bar, retracting | 415 N |
| Theoretical force at 6 bar, advancing | 482.5 N |
| Moving mass | 193 g |
| Product weight | 493 g |
| Type of mounting | With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | NBR TPE-U(PU) |
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | High-alloy stainless steel |