

Round cylinder DSNU-63-160-PPS-A

Part number: 559331

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Stroke | 160 mm |
| Piston diameter | 63 mm |
| Piston rod thread | M16x1.5 |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | Any |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | Via proximity switch |
| Symbol | 00992970 |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 1.3 J |
| Cushioning length | 21 mm |
| Theoretical force at 6 bar, retracting | 1681.9 N |
| Theoretical force at 6 bar, advancing | 1870.3 N |
| Moving mass | 859 g |
| Product weight | 2149 g |
| Type of mounting | With accessories |
| Pneumatic connection | G3/8 |
| Note on materials | RoHS compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | NBR TPE-U(PU) |
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | high-alloy stainless steel |