

Electric linear slide EGSK-26-200-2P

Part number: 562767

FESTO



General operating condition

Data sheet

| Feature | Value |
|--|----------------------------|
| Working stroke | 200 mm |
| Size | 26 |
| Reversing backlash | ≤20 μm |
| Screw diameter | 8 mm |
| Spindle pitch | 2 mm/U |
| Mounting position | Any |
| Guide | Recirculating ball bearing |
| Structural design | With ball screw |
| Homing | Reference switch |
| Spindle type | Ball screw |
| Symbol | 00991211 |
| Max. acceleration | 10 m/s ² |
| Max. speed | 0.28 m/s |
| Repetition accuracy | ±0.01 mm |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Degree of protection | IP10 |
| Ambient temperature | 0 °C ... 40 °C |
| Fixed bearing dynamic basic load rating | 1380 N |
| Linear guide dynamic basic load rating | 5746 N |
| Dynamic basic load rating, ball screw drive | 2350 N |
| 2nd moment of area ly | 17000 mm ⁴ |
| 2nd moment of area lz | 150000 mm ⁴ |
| Max. driving torque | 0.037 Nm |
| Max. force Fy | 2223 N |
| Max. force Fz | 2223 N |
| Max. torque Mx | 37.8 Nm |
| Max. torque My | 12.9 Nm |
| Max. torque Mz | 12.9 Nm |
| Max. feed force Fx | 116 N |
| No-load driving torque | 0.015 Nm |
| Ball screw drive statistical basic load rating | 4020 N |
| Linear guide statistical basic load rating | 12150 N |
| Mass moment of inertia JH per meter of stroke | 0.0316 kgcm ² |
| Mass moment of inertia JO | 0.00357 kgcm ² |

| Feature | Value |
|---------------------------------------|------------------------------------|
| Feed constant | 2 mm/U |
| Statistical fixed bearing load rating | 1760 N |
| Reference service life | 1000 km |
| Moving mass | 153 g |
| Slide weight | 153 g |
| Product weight | 1620 g |
| Additional slide weight | 153 g |
| Basic weight with 0 mm stroke | 780 g |
| Additional weight per 10 mm stroke | 42 g |
| Type of mounting | With internal thread and dowel pin |
| Material of end caps | Die-cast aluminum Coated |
| Profile material | high-alloy stainless steel |
| Note on materials | RoHS compliant |
| Drive cover material | Die-cast aluminum Coated |
| Slide material | Steel |
| Ball screw nut material | Steel |
| Spindle material | Steel |