

# Electric linear slide EGSK-33-600-6P

Part number: 562777

FESTO



 General operating condition

## Data sheet

Feature	Value
Working stroke	600 mm
Size	33
Reversing backlash	≤20 μm
Screw diameter	10 mm
Spindle pitch	6 mm/U
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	with ball screw drive
Homing	Reference switch
Spindle type	Ball screw drive
Symbol	00991211
Max. acceleration	20 m/s <sup>2</sup>
Max. speed	0.47 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C ... 40 °C
Fixed bearing dynamic basic load rating	1790 N
Linear guide dynamic basic load rating	9207 N
Dynamic basic load rating, ball screw drive	2840 N
2nd moment of area ly	62000 mm <sup>4</sup>
2nd moment of area lz	380000 mm <sup>4</sup>
Max. driving torque	0.14 Nm
Max. force Fy	2469 N
Max. force Fz	2469 N
Max. torque Mx	50.1 Nm
Max. torque My	16.4 Nm
Max. torque Mz	16.4 Nm
Max. feed force Fx	150 N
No-load driving torque	0.07 Nm
Ball screw drive statistical basic load rating	4900 N
Linear guide statistical basic load rating	20200 N
Mass moment of inertia JH per meter of stroke	0.0771 kgcm <sup>2</sup>
Mass moment of inertia JO	0.0115 kgcm <sup>2</sup>

<b>Feature</b>	<b>Value</b>
Feed constant	6 mm/U
Statistical fixed bearing load rating	2590 N
Reference service life	3000 km
Moving mass	310 g
Slide weight	310 g
Product weight	5160 g
Additional slide weight	310 g
Basic weight with 0 mm stroke	1380 g
Additional weight per 10 mm stroke	63 g
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	Coated High-alloy steel
Note on materials	RoHS-compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Ball screw nut material	Steel
Spindle material	Steel