

Electrical sub-base VAVE-L1-1L4-LR

Part number: 566729

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Reverse polarity protection | for operating voltage |
| Additional functions | Spark suppression Holding current reduction |
| Signal status display | LED |
| Nominal operating voltage DC | 24 V |
| Surge resistance | 0.8 kV |
| Contamination level | 3 |
| Certification | RCM compliance mark |
| CE marking (see declaration of conformity) | As per EU EMC directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP40 |
| Ambient temperature | -5 °C ... 60 °C |
| Mounting position | Any |
| Product weight | 33.5 g |
| Connection cross section | 0.14 mm ² |
| Electrical connection | Flying lead |
| Cable length | 5 m |
| Wire ends | Cable end sleeve |
| Protective earth connection | Not available |
| Type of mounting | Clip |
| Housing colour | Black |
| Note on materials | RoHS-compliant |
| Housing material | PA |