


Air solenoid valve VSVA-B-D52-ZD-D1-1R5L

Part number: 561375

FESTO



General operating condition

Data sheet

| Feature | Value |
|--|---|
| Valve function | 5/2-way, dominant, bistable |
| Actuation type | Electrical |
| Width | 42 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 1300 l/min |
| Pneumatic working port | Sub-base, size 1 according to ISO 5599-1 G1/4 |
| Operating voltage | 24V DC |
| Operating pressure | -0.09 MPa ... 1.6 MPa |
| Operating pressure | -0.9 bar ... 16 bar |
| Structural design | Piston gate valve |
| Certification | c UL us - recognized (OL) |
| Degree of protection | IP65 NEMA 4 |
| Nominal width | 11 mm |
| Width dimension | 43 mm |
| Exhaust air function | Adjustable Via throttle plate Via individual sub-base |
| Sealing principle | Soft |
| Mounting position | Any |
| Conforms to standard | ISO 5599-1 |
| Manual override | Detenting Non-detenting |
| Type of control | Piloted |
| Pilot air supply port | External |
| Flow direction | Any |
| Symbol | 00991750 |
| Lap | Positive overlap |
| Signal status display | LED |
| Pilot pressure MPa | 0.3 MPa ... 1 MPa |
| Pilot pressure | 3 bar ... 10 bar |
| Flow rate of pneumatic valve | 2000 l/min |
| Flow rate of pneumatic valve on individual sub-base | 1400 l/min |
| Optimized flow rate of pneumatic valve pneumatically concatenated flow | 1300 l/min |
| Changeover time | 19 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 1600 µs |

| Feature | Value |
|--|--|
| Max. negative test pulse on 1 signal | 1100 µs |
| Coil characteristics | 24 V DC: 1.6 W |
| Permissible voltage fluctuations | +/- 10% |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -5 °C ... 50 °C |
| Relative air humidity | 0 - 90% |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 439 g |
| Electrical connection | 3-pin M12x1 Central plug Round design |
| Type of mounting | On sub-base |
| Pilot air port 12/14 | Sub-base, size 1 as per ISO 5599-1 |
| Pilot exhaust air port 82/84 | Ducted Not ducted as per standard Alternatively: |
| Pneumatic connection 1 | Sub-base, size 1 as per ISO 5599-1 |
| Pneumatic connection 2 | Sub-base, size 1 as per ISO 5599-1 |
| Pneumatic connection 3 | Sub-base, size 1 as per ISO 5599-1 |
| Pneumatic connection 4 | Sub-base, size 1 as per ISO 5599-1 |
| Pneumatic connection 5 | Sub-base, size 1 as per ISO 5599-1 |
| Note on materials | RoHS compliant |
| Seals material | FPM HNBR NBR |
| Housing material | Die-cast aluminum PA |
| Material of screws | Steel Galvanized |