


Rotary actuator DSMI-40-270-A-B

Part number: 561691

FESTO



 General operating condition

Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg ... 270 deg
Stroke reduction in the end positions	5°
Shortest positioning stroke	5° when positioning 15° for Soft Stop
Piston diameter	40 mm
Swivel angle	0 deg ... 272 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position, positioning	Any
Mounting position, Soft Stop	Horizontal
Measuring principle of linear potentiometer	Analog
Structural design	Rotary vane
Position sensing	Via proximity switch With integrated angle measurement system
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure for positioning/soft stop	4 bar ... 8 bar
Max. swivel frequency at 6 bar	2 Hz
Max. travel speed	2000 deg/s
Min. travel speed	50 deg/s
Typical positioning time, short-stroke, horizontal	0.25/0.25 s
Typical positioning time, long stroke, horizontal	0.30/0.55 s
Connection resistance	5 kOhm
Recommended contact current	<1 µA
Mode of operation	Double-acting
Max. operating voltage DC	42 V
Max. short-time slider current	10000 µA
Max. current consumption	4 mA
Nominal operating voltage DC	10 V
Connection resistance tolerance	20 %
Permissible voltage fluctuations	<1%
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Operating medium	Compressed air as per ISO 8573-1:2010 [6:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Continuous shock resistance to DIN/IEC 68 Part 2-82	Tested as per severity level 2
Corrosion resistance class (CRC)	0 - No corrosion stress

Feature	Value
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65 As per IEC 60529
Vibration resistance to DIN/IEC 68 Part 2-6	Tested as per severity level 2
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	0.1 J
Max. axial force	120 N
Max. mass moment of inertia, horizontal	0.12 kgm ²
Max. mass moment of inertia, vertical	0.12 kgm ²
Max. radial force	350 N
Min. mass moment of inertia, horizontal	0.006 kgm ²
Min. mass moment of inertia, vertical	0.006 kgm ²
Theoretical torque at 6 bar	20 Nm
Product weight	3950 g
Angular resolution	≤0.1 deg
Output signal	Analog
Independent linearity	0.0025
Positioning repetition accuracy	+/- 0.3 deg
Soft Stop end position repetition accuracy	< 0.2 deg
Repetition accuracy, Soft Stop intermediate position	+/- 2 deg
Linear potentiometer electrical connection	4-pin
Cable length	30 m
Type of mounting	With internal thread
Pneumatic connection	G1/8
Material of measuring system housing	Wrought aluminum alloy Anodized
Stop lever material	Wrought aluminum alloy Anodized
Drive shaft material	Steel, nickel-plated
(Fixed) stop material	Steel
Housing material	Anodized
Measuring system coupling material	TPE-U(PU)
Feather key material	Steel
Vane material	Reinforced PET
Material of plug housing	PA-reinforced
Material of cylinder barrel	Wrought aluminum alloy