

# Handling module HSW-10-AP-AW

Part number: 562559

FESTO



 General operating condition

## Data sheet

Feature	Value
Working stroke	9 mm ... 15 mm
Size	10
Max. linear stroke at 90° swivel angle	90/90 mm
Maximum wait position module Z-stroke	10 mm
Z-stroke	80 mm ... 100 mm
Cushioning	Pneumatic shock absorber at both ends Soft characteristic curve
Mounting position	Any
Structural design	Linear guide plus ball bearing Quarter turn actuator Positively driven motion sequence
Position sensing	For proximity sensor
Operating pressure	4 bar ... 8 bar
Minimum cycle time	0.6 s
Repetition accuracy end positions	+/-0.02 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. torque Mx	0.6 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Max. payload	0.5 kg
Maximum process force in y direction	30 N
Theoretical force at 6 bar	30 N
Product weight	1360 g
Type of mounting	Via through-hole and centering sleeve
Wait position pneumatic connection	M5
Pneumatic connection	M3
Stops material	High-alloy steel
Spring pressure piece material	High-alloy steel
Base plate material	Wrought aluminum alloy Anodized
Retainer bracket material	Anodized
Cross guide material	Tempered steel
Swivel lever material	Case-hardened steel Burnished

<b>Feature</b>	<b>Value</b>
Link material	Case-hardened steel Hardened
Sensor rail material	Wrought aluminum alloy Anodized
Fixed link material	Wrought aluminum alloy Anodized
Setting screw material	High-alloy steel