

Electric linear slide EGSK-26-150-6P

Part number: 562770

FESTO



General operating condition

Data sheet

Feature	Value
Working stroke	150 mm
Size	26
Reversing backlash	≤20 μm
Screw diameter	8 mm
Spindle pitch	6 mm/U
Mounting position	Any
Guide	Recirculating ball bearing
Structural design	With ball screw
Homing	Reference switch
Spindle type	Ball screw
Symbol	00991211
Max. acceleration	10 m/s ²
Max. speed	0.59 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Degree of protection	IP10
Ambient temperature	0 °C ... 40 °C
Fixed bearing dynamic basic load rating	1380 N
Linear guide dynamic basic load rating	5746 N
Dynamic basic load rating, ball screw drive	1950 N
2nd moment of area ly	17000 mm ⁴
2nd moment of area lz	150000 mm ⁴
Max. driving torque	0.11 Nm
Max. force Fy	1541 N
Max. force Fz	1541 N
Max. torque Mx	26.2 Nm
Max. torque My	8.9 Nm
Max. torque Mz	8.9 Nm
Max. feed force Fx	116 N
No-load driving torque	0.015 Nm
Ball screw drive statistical basic load rating	3510 N
Linear guide statistical basic load rating	12150 N
Mass moment of inertia JH per meter of stroke	0.0316 kgcm ²
Mass moment of inertia JO	0.00481 kgcm ²

Feature	Value
Feed constant	6 mm/U
Statistical fixed bearing load rating	1760 N
Reference service life	3000 km
Moving mass	153 g
Slide weight	153 g
Product weight	1410 g
Additional slide weight	153 g
Basic weight with 0 mm stroke	780 g
Additional weight per 10 mm stroke	42 g
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	high-alloy stainless steel
Note on materials	RoHS compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Ball screw nut material	Steel
Spindle material	Steel