

Mini slide DGSL-16-50-EA

Part number: 570191

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	50 mm
Adjustable end-position range/front length	3.5 mm
Adjustable end-position range/rear length	5.5 mm
Piston diameter	20 mm
Drive unit operating mode	Yoke
Cushioning	Short elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991263
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Max. speed	0.8 m/s
Repetition accuracy	0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Ambient temperature	0 °C ... 60 °C
Impact energy in the end positions	0.35 J
Cushioning length	1.2 mm
Max. force F _y	2780 N
Max. force F _z	2780 N
Max. torque M _x	40 Nm
Max. torque M _y	25 Nm
Max. torque M _z	25 Nm
Theoretical force at 6 bar, retracting	158 N
Theoretical force at 6 bar, advancing	188 N
Moving mass	519 g
Product weight	1173 g

Feature	Value
Alternative connections	See product drawing
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel