

Radial gripper HGRT-32-A-G2

Part number: 563911

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Max. interchangeability	≤0.2 mm
Max. gripper jaw angular play ax, ay	≤0.1 deg
Max. opening angle	180 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.02 mm
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Radial
Gripping force backup	During closing
Structural design	Positively driven motion sequence
Position sensing	Via proximity switch For inductive sensors
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	503 ms
Min. closing time at 6 bar	337 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	5.03 kgcm ²
Maximum force on gripper jaw Fz, static	280 N
Maximum torque on gripper jaw, My static	13.5 Nm
Maximum torque on gripper jaw, Mz static	1.3 Nm
Relubrication interval for guidance elements	10 MioCyc
Product weight	940 g
Type of mounting	With internal thread and centering sleeve
Pneumatic connection	M5
Note on materials	RoHS compliant
Housing material	Wrought aluminum alloy, smooth-anodized
Gripper jaw material	Hardened steel