


Axial kit EAMM-A-P8-38A-70A

Part number: 564996

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|------------------------|
| Nominal length | 13.75 mm |
| Mounting position | Any |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 5.87 kgmm ² |
| Transferable torque | 12.5 Nm |
| Product weight | 200 g |
| Interface code, actuator | P8-38A |
| Interface code, motor in | 70A |
| Interface code, coupling housing | 38A |
| Note on materials | RoHS compliant |