

Bus node CTEU-EC

Part number: 572556

FESTO



 General operating condition

Data sheet

Feature	Value
Protocol	EtherCAT
Dimensions W x L x H	40 mm x 91 mm x 50 mm
Width dimension	40 mm
Type of mounting	On electrical interface On electrical sub-base
Product weight	90 g
Ambient temperature	0 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Degree of protection	IP65 IP67
Note on degree of protection	In mounted state Unused connections sealed
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC characters	KC EMC
Certification	RCM compliance mark c UL us - Listed (OL)
Note on materials	RoHS-compliant
Housing material	PA
LED display (product-specific)	PS: operating voltage for electronics and load supply X1: module system status at I-Port 1 X2: module system status at I-Port 2
LED display (bus-specific)	L/A1: network active, port 1 L/A2: network active, port 2 Run: communication status
Diagnostics	Communication error System diagnostics Undervoltage
Control elements	DIL switch
Fieldbus interface, type	Ethernet
Fieldbus interface, protocol	EtherCAT
Fieldbus interface, function	Bus connection, incoming/forwarding
Fieldbus interface, connection type	2x socket
Fieldbus interface, connection technology	M12x1, D-coded as per EN 61076-2-101
Fieldbus interface, connection pattern	00995716
Fieldbus interface, number of poles/wires	4

Feature	Value
Fieldbus interface, galvanic isolation	yes
Fieldbus interface, transmission rate	100 Mbit/s
Max. address capacity inputs	16 byte
Max. address capacity outputs	16 byte
Parameterization	Activate diagnostics Fail-safe and idle response
Internal cycle time	1 ms per 1 byte of user data
Configuration support	XML file
Additional functions	Modular Device Profile (MDP)
Power supply, function	Electronics and load
Power supply, type of connection	Plug
Power supply, connection technology	M12x1, A-coded as per EN 61076-2-101
Power supply, connection pattern	00995383
Power supply, number of pins/wires	5
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Max. power supply	4 A
Intrinsic current consumption at nominal operating voltage	Typ. 60 mA