

Manifold rail VABM-L1-10HW-G18-6-GR

Part number: 573436

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Width dimension | 10.5 mm |
| Mounting position | Any |
| Max. no. of valve positions | 6 |
| Certification | c UL us - Recognized (OL) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Storage temperature | -20 °C ... 60 °C |
| Product weight | 464 g |
| Pilot air port 12/14 | M5 |
| Pilot exhaust air port 82/84 | M5 |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | M7 |
| Pneumatic connection 3 | G1/8 |
| Pneumatic connection 4 | M7 |
| Pneumatic connection 5 | G1/8 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |