

# Input module CPX-L-16DE-16-KL-3POL

Part number: 572606

FESTO



 General operating condition

## Data sheet

Feature	Value
Dimensions W x L x H	50 mm x 107 mm x 41 mm
Product weight	167 g
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Degree of protection	IP20
Corrosion resistance class (CRC)	(when installed)
LABS (PWIS) conformity	VDMA24364-B2-L
Certification	c UL us - Listed (OL)
Note on materials	RoHS-compliant
Housing material	PA-reinforced
LED indicators	1 group diagnostics 16 channel status
Diagnostics	Short circuit/overload per channel
Parameterization	Input debounce time Signal extension time Response to short circuit Module monitoring
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Intrinsic current consumption at nominal operating voltage	Typ. 15 mA
No. of inputs	16
Input characteristics	IEC1131-T2, type 01
Switching level	Signal 0: $\leq 5$ V Signal 1: $\geq 15$ V
Input switching logic	PNP (positive switching)
Input debounce time	3 ms (0.1 ms, 10 ms, 20 ms parameterizable)
Max. residual current of inputs per module	1.8 A
Electrical isolation between channels	no
Electrical isolation between channel and internal bus	no
Fuse protection (short circuit)	Internal electronic fuse per module