

Compact cylinder ADNGF-80-30-PPS-A

Part number: 574062

FESTO



 General operating condition

Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	80 mm
Based on norm	ISO 21287
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Protection against torsion/guide	Guide rod with yoke
Operating pressure	0.14 MPa ... 1 MPa
Operating pressure	1.4 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	8 J
Cushioning length	7.5 mm
Theoretical force at 6 bar, retracting	2827 N
Theoretical force at 6 bar, advancing	3016 N
Moving mass	897 g
Product weight	1766 g
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Flange screws material	Steel
Cover material	Die-cast aluminum, coated
Seals material	TPE-U(PUR)
End plate material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized