


# Pneumatic valve VUWG-L14-T32U-M-G18

Part number: 574260

FESTO



[PDF General operating condition](#)

## Data sheet

Feature	Value
Valve function	2x3/2 open monostable
Actuation type	Pneumatic
Valve size	14 mm
Normal nominal flow rate (normalized to DIN 1343)	410 l/min
Pneumatic working port	G1/8
Operating pressure	-0.9 bar ... 10 bar
Structural design	Piston gate valve
Reset method	Mechanical spring
Width dimension	16 mm
Exhaust air function	Adjustable
Sealing principle	Soft
Mounting position	Any
Manual override	None
Type of control	directly
Flow direction	Reversible
Symbol	00992943
Lap	Positive overlap
Pilot pressure	3 bar ... 10 bar
Suitability for vacuum	Yes
Switching time off	13 ms
On switching time	9 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Temperature of medium	-5 °C ... 50 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-5 °C ... 60 °C
Product weight	77 g
Type of mounting	On PR manifold rail With through-hole
Pilot air port 12	M5
Pilot air port 14	M5
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8

<b>Feature</b>	<b>Value</b>
Pneumatic connection 3	G1/8
Pneumatic connection 4	G1/8
Pneumatic connection 5	G1/8
Note on materials	RoHS compliant
Seals material	HNBR NBR
Housing material	Anodized