

# Air solenoid valve

## VUVS-L25-M32C-MD-G14-F8-1C1

FESTO

Part number: 575477



General operating condition

## Data sheet

| Feature                                           | Value                                                              |
|---------------------------------------------------|--------------------------------------------------------------------|
| Valve function                                    | 3/2, closed, monostable                                            |
| Actuation type                                    | Electrical                                                         |
| Valve size                                        | 26.5 mm                                                            |
| Normal nominal flow rate (normalized to DIN 1343) | 1000 l/min                                                         |
| Pneumatic working port                            | G1/4                                                               |
| Operating voltage                                 | 24V DC                                                             |
| Operating pressure                                | 0.25 MPa ... 1 MPa                                                 |
| Operating pressure                                | 2.5 bar ... 10 bar                                                 |
| Structural design                                 | Piston gate valve                                                  |
| Reset method                                      | Mechanical spring                                                  |
| Certification                                     | c UL us - Recognized (OL)                                          |
| Degree of protection                              | IP65<br>With plug socket<br>as per IEC 60529                       |
| Nominal width                                     | 6.3 mm                                                             |
| Exhaust air function                              | With flow control option                                           |
| Sealing principle                                 | Soft                                                               |
| Mounting position                                 | Any                                                                |
| Manual override                                   | Detenting<br>Non-detenting                                         |
| Type of control                                   | Pilot-controlled                                                   |
| Pilot air supply port                             | Internal                                                           |
| Flow direction                                    | Non-reversible                                                     |
| Symbol                                            | 00991041                                                           |
| Lap                                               | Overlap                                                            |
| b-value                                           | 0.3                                                                |
| C value                                           | 4.8 l/sbar                                                         |
| Switching time off                                | 40 ms                                                              |
| On switching time                                 | 11 ms                                                              |
| Duty cycle                                        | 100%                                                               |
| Max. positive test pulse with 0 signal            | 2000 µs                                                            |
| Max. negative test pulse on 1 signal              | 3600 µs                                                            |
| Coil characteristics                              | 24 V DC: 3.3 W                                                     |
| Permissible voltage fluctuations                  | +/- 10 %                                                           |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media          | Operation with oil lubrication possible (required for further use) |

| Feature                                                   | Value                                                                                |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------|
| Vibration resistance                                      | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance                                          | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                |
| Corrosion resistance class (CRC)                          | 2 - Moderate corrosion stress                                                        |
| LABS (PWIS) conformity                                    | VDMA24364-B1/B2-L                                                                    |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1                                                     |
| Temperature of medium                                     | -10 °C ... 60 °C                                                                     |
| Pilot medium                                              | Compressed air as per ISO 8573-1:2010 [7:4:4]                                        |
| Ambient temperature                                       | -10 °C ... 60 °C                                                                     |
| Product weight                                            | 297 g                                                                                |
| Electrical connection                                     | Form C<br>as per EN 175301-803                                                       |
| Type of mounting                                          | On terminal strip<br>With through-hole                                               |
| Venting hole connection                                   | Not ducted                                                                           |
| Pilot exhaust air port 82                                 | M5                                                                                   |
| Pneumatic connection 1                                    | G1/4                                                                                 |
| Pneumatic connection 2                                    | G <sup>1</sup> / <sub>4</sub>                                                        |
| Pneumatic connection 3                                    | G1/4                                                                                 |
| Note on materials                                         | RoHS-compliant                                                                       |
| Seals material                                            | HNBR<br>NBR                                                                          |
| Housing material                                          | Die-cast aluminum<br>Painted                                                         |
| Piston slide material                                     | Wrought aluminum alloy                                                               |
| Material of screws                                        | Steel, galvanized                                                                    |