


Pneumatic timer VZ-3-PK-3

Part number: 5755

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal width	2 mm
Actuation type	Pneumatic
Structural design	Poppet valve with spring return
Symbol	00991130
Lap	Negative overlap
Note on forced dynamization	Switching frequency at least once a week
Operating pressure	2.5 bar ... 8 bar
Normal nominal flow rate (normalized to DIN 1343)	90 l/min
Adjustable delay time	0.25 s ... 5 s
Pause period for reset	≥55 ms
Repetition accuracy of time setting	± 0.5 s
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 60 °C
Product weight	150 g
Type of mounting	On mounting frame
Pneumatic connection	PK-3
Housing material	Die-cast zinc