

# Electrical sub-base VAVE-L1-1R1-LR

Part number: 573922

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value   |
|--|---|
| Reverse polarity protection                  | Bipolar                                       |
| Additional functions                         | Spark arresting<br>Holding current reduction  |
| Signal status display                        | LED   |
| Nominal operating voltage DC                 | 24 V  |
| Surge resistance                             | 0.8 kV  |
| Contamination level                          | 3   |
| Certification                                | RCM compliance mark                           |
| CE marking (see declaration of conformity)   | As per EU EMC directive                       |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC                    |
| Corrosion resistance class (CRC)             | 2 - Moderate corrosion stress                 |
| LABS (PWIS) conformity                       | VDMA24364-B2-L                                |
| Degree of protection                         | IP65  |
| Ambient temperature                          | -5 °C ... 60 °C                               |
| Mounting position                            | Any   |
| Max. tightening torque                       | 0.27 Nm                                       |
| Product weight                               | 3.2 g   |
| Electrical connection                        | M8 / -<br>Plug / socket                       |
| Protective earth connection                  | Not available                                 |
| Type of mounting                             | On air solenoid valve with self-tapping screw |
| Housing colour                               | Black   |
| Note on materials                            | RoHS compliant                                |
| Cover material                               | PA  |
| Seals material                               | EPDM  |
| Housing material                             | PA  |
| Material of screws                           | Quenched and tempered steel                   |