

Electric cylinder ESBF-BS-63-300-5P

Part number: 574094

FESTO



 General operating condition

Data sheet

Feature	Value
Working stroke	300 mm
Size	63
Stroke	300 mm
Piston rod thread	M16x1.5
Reversing backlash	30 µm
Screw diameter	25 mm
Spindle pitch	5 mm/U
Max. angle of rotation of the piston rod +/-	0.4 deg
Based on norm	ISO 15552
Mounting position	Any
Piston rod end	External thread
Motor type	Servo motor
Position sensing	Via proximity switch
Structural design	Electric cylinder with ball screw
Spindle type	Ball screw
Symbol	00991941
Protection against torsion/guide	With plain bearing-guide
Max. acceleration	5 m/s ²
Max. rotational speed	3250 rpm
Max. speed	0.27 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-20 °C ... 60 °C
For use in the food industry	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C ... 60 °C
Max. driving torque	7 Nm
Max. radial force on actuator shaft	700 N
Max. feed force F _x	7000 N
No-load driving torque	0.4 Nm
Guide value for payload, horizontal	700 kg
Guide value for payload, vertical	700 kg
Mass moment of inertia J _H per meter of stroke	2.8316 kgcm ²

Feature	Value
Mass moment of inertia JL per kg of payload	0.00633 kgcm ²
Mass moment of inertia JO	0.49112 kgcm ²
Maintenance interval	Lifetime lubrication
Moving mass at 0 mm stroke	1829 g
Additional moving mass per 10 mm stroke	52 g
Basic weight with 0 mm stroke	3163 g
Additional weight per 10 mm stroke	87 g
Type of mounting	With internal thread or accessories
Interface code, actuator	D60
Note on materials	RoHS compliant
Cover material	Die-cast aluminum, coated
Piston rod material	high-alloy stainless steel
Material of screws	Galvanized steel
Ball screw nut material	Bearing steel
Spindle material	Bearing steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized