

Compact cylinder ADN-100-60-A-PPS-A

Part number: 577206

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	60 mm
Piston diameter	100 mm
Piston rod thread	M16x1.5
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Conforms to standard	ISO 21287
Piston rod end	External thread
Position sensing	For proximity sensor
Symbol	00991217
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	2.5 J
Cushioning length	10 mm
Theoretical force at 6 bar, retracting	4524 N
Theoretical force at 6 bar, advancing	4712 N
Moving mass	769 g
Product weight	2357 g
Type of mounting	With through-hole With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Flange screws material	Steel
Cover material	Die-cast aluminum, coated
Seals material	TPE-U(PUR)
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized