

Input/output module CPX-2ZE2DA

Part number: 576046

FESTO



 General operating condition

Data sheet

Feature	Value
Dimensions W x L x H	50 mm x 107 mm x 50 mm
Width dimension	50 mm
Product weight	130 g
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	(when installed)
Max. cable length	30 m
LABS (PWIS) conformity	VDMA24364-B2-L
Certification	UL - Recognized (OL)
Note on materials	RoHS-compliant
Housing material	Polymer
LED indicators	1 group diagnostics 10 channel status 2 module diagnostics 2 channel diagnostics
Diagnostics	Operating-mode-dependent diagnostics
No. of outputs	2
Parameterization	On/off delay Frequency output Speed measurement Pulse output Pulse train Rotational speed measurement Frequency measurement Period duration measurement Motor operating mode Position determination Pulse width modulation One-off counting Infinite counting Periodic counting
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Intrinsic current consumption at nominal operating voltage	Typ. 35 mA
No. of inputs	2
Input characteristics	As per IEC 1131-2, type O2
Switching level	Signal 0: ≤ 5 V Signal 1: ≥ 11 V
Input switching logic	PNP (positive switching)

Feature	Value
Input debounce time	0.1 μ s (0.2 μ s,0.4 μ s,0.8 μ s,1 μ s,2 μ s,4 μ s,8 μ s,10 μ s,50 μ s,100 μ s,500 μ s,1ms,3ms,10ms,20ms parameterizable)
Max. residual current of inputs per module	2 A
Characteristic curve outputs	IEC1131-T2
Switching logic at outputs	NPN (negative switching) PNP (positive switching) Push-pull driver
Max. residual current of outputs per module	10 A
Max. power supply per channel	5 A adjustable (20 W lamp load)
Electrical isolation between channels	no
Electrical isolation between channel and internal bus	Outputs - yes, when using an intermediate supply
Fuse protection (short circuit)	Internal electronic fuse per channel