

Pneumatic valve VUWS-LT20-T32H-M-N18

Part number: 577538

FESTO



General operating condition

Data sheet

| Feature | Value |
|---|--|
| Valve function | 2x3/2, open/closed, monostable |
| Actuation type | Pneumatic |
| Valve size | 21 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 600 l/min |
| Pneumatic working port | 1/8 NPT |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Structural design | Plate seat |
| Reset method | Mechanical spring |
| Certification | c UL us - Recognized (OL) |
| Nominal width | 5.2 mm |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | None |
| Type of control | Direct |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Symbol | 00995853 |
| Lap | Underlap |
| Pilot pressure MPa | 0.15 MPa ... 1 MPa |
| Pilot pressure | 1.5 bar ... 10 bar |
| Switching time off | 19 ms |
| On switching time | 6 ms |
| Explosion prevention and protection | Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |

| Feature | Value |
|-------------------------|---|
| Temperature of medium | -10 °C ... 60 °C |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 60 °C |
| Product weight | 154 g |
| Type of mounting | On terminal strip With through-hole |
| Venting hole connection | Not ducted |
| Pilot air port 10 | 10-32 UNF-2B |
| Pilot air port 14 | 10-32 UNF-2B |
| Pneumatic connection 1 | 1/8 NPT |
| Pneumatic connection 2 | 1/8 NPT |
| Pneumatic connection 3 | 1/8 NPT |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR TPE-U(PU) |
| Housing material | Painted |
| Material of screws | Steel, galvanized |