



# Air solenoid valve VMPA2-M1BH-J-PI

Part number: 8022035

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function                                    | 5/2-way, bistable  |
| Actuation type                                    | Electrical   |
| Valve size  | 20 mm  |
| Normal nominal flow rate (normalized to DIN 1343) | 860 l/min  |
| Operating voltage                                 | 24V DC   |
| Operating pressure                                | -0.09 MPa ... 1 MPa  |
| Operating pressure                                | -0.9 bar ... 10 bar  |
| Structural design                                 | Piston gate valve  |
| Certification                                     | c UL us - recognized (OL)  |
| Degree of protection                              | IP65<br>As per IEC 60529   |
| Sealing principle                                 | Soft   |
| Mounting position                                 | Any  |
| Manual override                                   | Detenting<br>Non-detenting   |
| Type of control                                   | Piloted  |
| Flow direction                                    | Reversible   |
| Symbol  | 00991067   |
| Lap   | Positive overlap   |
| Signal status display                             | Yes  |
| Pilot pressure MPa                                | 0.3 MPa ... 0.8 MPa  |
| Pilot pressure                                    | 3 bar ... 8 bar  |
| Suitability for vacuum                            | Yes  |
| Standard nominal flow rate with QS-10             | 860 l/min  |
| On switching time                                 | 9 ms   |
| Changeover time                                   | 22 ms  |
| Max. positive test pulse with 0 signal            | 400 µs   |
| Max. negative test pulse on 1 signal              | 900 µs   |
| Permissible voltage fluctuations                  | +/- 25%  |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [7:4:4]  |
| Information on operating and pilot media          | Operation with oil lubrication possible (required for further use)                   |
| Vibration resistance                              | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance                                  | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                |
| Corrosion resistance class (CRC)                  | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                            | VDMA24364-B1/B2-L  |

| <b>Feature</b>                            | <b>Value</b>      |
|---|-------------------|
| Storage temperature                       | -20 °C ... 40 °C  |
| Temperature of medium                     | -5 °C ... 50 °C   |
| Relative air humidity                     | Max. 90% at 40°C  |
| Ambient temperature                       | -5 °C ... 50 °C   |
| Max. tightening torque for valve mounting | 0.65 Nm           |
| Product weight                            | 100 g             |
| Type of mounting                          | With through-hole |
| Note on materials                         | RoHS compliant    |
| Seals material                            | NBR               |
| Housing material                          | Die-cast aluminum |