

Electric cylinder ESBF-...-40- -

Part number: 8022585

FESTO



 General operating condition

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	40
Stroke	30 mm ... 800 mm
Piston rod thread	M12x1.25
Screw diameter	16 mm
Max. angle of rotation of the piston rod +/-	0.2 deg
Based on norm	ISO 15552
Mounting position	Any
Motor type	Stepper motor Servo motor
Position sensing	Via proximity switch
Structural design	Electric cylinder with ball screw Electric cylinder with lead screw spindle
Symbol	00991941
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Protection against torsion/guide	With plain bearing-guide
Duty cycle	100%
Corrosion resistance class (CRC)	2 - Moderate corrosion stress 3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Storage temperature	-20 °C ... 60 °C
For use in the food industry	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40 IP65
Ambient temperature	0 °C ... 60 °C
Max. radial force on actuator shaft	130 N
Max. feed force F _x	3000 N
No-load driving torque	0.2 Nm
Type of mounting	With internal thread or accessories
Interface code, actuator	D40
Note on materials	RoHS compliant

Feature	Value
Cover material	Wrought aluminum alloy, smooth-anodized
Piston rod material	high-alloy stainless steel
Material of screws	Galvanized steel
Ball screw nut material	Bearing steel
Spindle material	Bearing steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized