


Air solenoid valve VMPA14-M1HF-E-PI

FESTO

Part number: 578808



[General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/3, exhausted |
| Actuation type | Electrical |
| Valve size | 14 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 420 l/min ... 480 l/min |
| Operating voltage | 24V DC |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Certification | c UL us - Recognized (OL) |
| Degree of protection | IP65 In mounted state as per IEC 60529 |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting |
| Type of control | Pilot-controlled |
| Flow direction | Reversible |
| Symbol | 00991032 |
| Lap | Overlap |
| Signal status display | yes |
| Pilot pressure MPa | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| Suitability for vacuum | yes |
| Note on standard nominal flow rate | MPA-C: 550 l/min MPA-L: 480 l/min MPA-S: 420 l/min |
| Standard nominal flow rate with QS-8 | 420 l/min ... 550 l/min |
| Switching time off | 40 ms |
| On switching time | 12 ms |
| Changeover time | 18 ms |
| Max. positive test pulse with 0 signal | 400 µs |
| Max. negative test pulse on 1 signal | 200 µs |
| Permissible voltage fluctuations | +/- 25 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |

| Feature | Value |
|---|--|
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 40 °C |
| For use in the food industry | See supplementary material information |
| Temperature of medium | -5 °C ... 50 °C |
| Relative air humidity | Max. 90 % at 40 °C |
| Ambient temperature | -5 °C ... 60 °C |
| Max. tightening torque for valve mounting | 0.65 Nm |
| Product weight | 77 g |
| Type of mounting | With through-hole |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Housing material | Die-cast aluminum |