

Solenoid coil VACS-C-C1-1

Part number: 8025330

FESTO



 General operating condition

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100%
Insulation class	H
Coil characteristics	24 V DC: 2.6 W
Permissible voltage fluctuations	+/- 10 %
Certification	c UL us - Recognized (OL)
Certificate issuing authority	UL MH18122
Restricted ambient and media temperature	-10 - 50 °C
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-10 °C ... 60 °C
Product weight	35.2 g
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	Connection diagram type C as per EN 175301-803
Electrical connection 1, number of pins/wires	3
Electrical connection for input 1, connection pattern	00995860
Electrical connection 1, type of mounting	Central screw M2.5
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper