


Solenoid coil VACN-N-A1-1-EX4-A

Part number: 8029139

FESTO



 General operating condition

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Duty cycle	100%
Required current consumption	≥0.027 A
Insulation class	F
Enameled wire insulation class	H
Max. input voltage V_i	28 V
Max. input current I_i	115 mA
Effective internal capacitance C_i	Negligibly low
Effective internal inductance L_i	Negligibly low
Maritime classification	See certificate
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity)	acc. to UK EX instructions
Explosion protection certification outside the EU	EPL Db (BR) EPL Db (CN) EPL Db (GB) EPL Db (IEC-EX) EPL Gb (BR) EPL Gb (CN) EPL Gb (GB) EPL Gb (IEC-EX)
Explosion prevention and protection	Zone 1 (ATEX) Zone 1 (BR) Zone 1 (CN) Zone 1 (IEC-EX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (BR) Zone 21 (CN) Zone 21 (IEC-EX) Zone 21 (UKEX) Zone 22 (ATEX)
Certificate issuing authority	CCC 2021322307003993 DNV 15.0188 DNV TAA000011J GYJ21.1326 IECEX PTB 15.0013 PTB 09 ATEX 2043
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex ia IIC/IIB T6/T4 Gb

Feature	Value
Type of (ignition) protection for dust	Ex tb IIIC T80°C/T130°C Db
Explosive ambient temperature	T4, T130°C: -40°C ≤ Ta ≤ +85°C T6, T80°C: -40°C ≤ Ta ≤ +50°C
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Product weight	114 g
Electrical connection	Form A as per DIN EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	Polymer Steel
Material of pin contacts	Brass
Material of winding	Copper