

Solenoid valve

VUVG-B18-T32H-AZ-F-P1

FESTO

Part number: 8033561



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------------------------|----------------------------------------------------------------------------------------|
| Valve function | 2x3/2, open/closed, monostable |
| Actuation type | Electrical |
| Valve size | 18 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 790 l/min |
| Pneumatic working port | Flange |
| Operating pressure | 0.15 MPa ... 1 MPa |
| Operating pressure | 1.5 bar ... 10 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Certification | c UL us - recognized (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions To UK instructions for electrical equipment |
| Certificate issuing authority | UL MH19482 |
| Degree of protection | IP65 With electrical pilot valve and plug socket |
| Nominal width | 5.7 mm |
| Exhaust air function | Adjustable |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of control | Piloted |
| Pilot air supply port | External |
| Symbol | 00992909 |
| Lap | Positive overlap |
| Pilot pressure MPa | 0.15 MPa ... 0.8 MPa |
| Pilot pressure | 1.5 bar ... 8 bar |
| Switching time off | 18 ms |
| On switching time | 13 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 700 µs |
| Max. negative test pulse on 1 signal | 900 µs |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |

| Feature | Value |
|-----------------------------------------------------------|-----------------------------------------------------------------------|
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1 |
| Temperature of medium | -5 °C ... 60 °C |
| Ambient temperature | -5 °C ... 60 °C |
| Product weight | 140 g |
| Electrical connection | Via electric pilot valve |
| Type of mounting | On terminal strip |
| Pilot interface | As per ISO 15218 |
| Note on materials | RoHS compliant |
| Seals material | HNBR NBR |
| Housing material | Wrought aluminum alloy |