

Solenoid coil VACF-B-C1-5

Part number: 8030810

FESTO



 General operating condition

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100%
Insulation class	H
Coil characteristics	12 V DC: 3.4 W
Permissible voltage fluctuations	+/- 10%
Certification	c UL us - recognized (OL)
Certificate issuing authority	UL MH18122
Restricted ambient and media temperature	-20 - 50 °C
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-20 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	52.4 g
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	Connection diagram type C as per EN 175301-803
Electrical connection 1, number of pins/wires	3
Electrical connection for input 1, connection pattern	00995860
Electrical connection 1, type of mounting	Central screw M2.5
Type of mounting	With knurled nut
Note on materials	RoHS compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplast
Material of winding	Copper